

PHOTON IS OUR BUSINESS

# MPPC<sup>®</sup> (Multi-Pixel Photon Counter)



S14422 series

# High sensitivity, low noise MPPC for visible and near infrared region

MPPC, also called SiPM (silicon photomultiplier), is a new type of photon counting device that consists of multiple Geiger mode APD (avalanche photodiode) pixels. It is an opto-semiconductor with outstanding photon counting capability and low operating voltage and is immune to the effects of magnetic fields.

The S14422 series is an MPPC for the visible to near infrared region. It provides higher photon detection efficiency than the previous product (S13362 series) in the visible to near infrared region. In addition, the built-in TE-cooler function provides low crosstalk and low afterpulses as well as reduces the dark count to 1/10 that of the non-cooled type (S14420 series).

#### Features

- Low dark count: 1/10 that of the non-cooled type (-10 °C)
- High photon detection efficiency: 40% (λ=600 nm, Vop=VBR + 5, 50 μm pitch)
- **■** Low crosstalk, low afterpulses
- Low voltage (VBR=40.5 V typ.) operation (-10 °C)
- **→** High gain: 10<sup>5</sup> to 10<sup>6</sup>
- Operates with simple readout circuit
- MPPC module also available (sold separately)

#### Applications

- **→** Laser scan microscope
- Fluorescence measurement

#### Structure

Parameter	S14422-1525DG	S14422-1550DG	S14422-3025DG	S14422-3050DG	Unit	
Pixel pitch	25	50	25	50	μm	
Effective photosensitive area	φ1	1.5	ф3	mm		
Number of pixels	2876	724	11344	2836	-	
Fill factor	63	81	63	81	%	
Package	Metal (TO-8)					
Window material	Borosilicate glass					
Window refractive index	1.52					
Cooling	Two-stage TE-cooled					

#### - Absolute maximum ratings

Parameter	Symbol	S14422-1525DG	S14422-1550DG	S14422-3025DG	S14422-3050DG	Unit
Operating temperature*1	Topr	-20 to +60				°C
Storage temperature*1	Tstg	-20 to +85				°C
Chip temperature	Tchip	-25 to ambient temperature				°C
Thermistor power dissipation	Pd_th	0.2			mW	
Allowable TE-cooler current	ITE max	1		Α		
Allowable TE-cooler voltage	VTE max	0.9		٧		
Soldering conditions*2	Tsol	Peak temperature: 350 °C*3, once, 3 s max.			-	

<sup>\*1:</sup> No dew condensation

When there is a temperature difference between a product and the surrounding area in high humidity environment, dew condensation may occur on the product surface. Dew condensation on the product may cause deterioration in characteristics and reliability.

Note: Exceeding the absolute maximum ratings even momentarily may cause a drop in product quality. Always be sure to use the product within the absolute maximum ratings.

<sup>\*2:</sup> At least 1 mm away from lead roots

<sup>\*3:</sup> Soldering iron tip


# **■** Electrical and optical characteristics (Typ. Ta=25 °C, Tchip=-10 °C, unless otherwise noted)

Parameter	•	Symbol	S14422-1525DG	S14422-1550DG	S14422-3025DG	S14422-3050DG	Unit
Spectral response range		λ	350 to 1000			nm	
Peak sensitivity waveleng	th	λр	600			nm	
Photon detection efficience	Photon detection efficiency*4		30	40	30	40	%
Dark count Typ. Max.	Тур.		3	5	140		kene
	Max.	_	90		350		kcps
Terminal capacitance		Ct	90		350		pF
Gain		М	$0.9 \times 10^{6}$	$3.6 \times 10^{6}$	$0.9 \times 10^{6}$	$3.6 \times 10^{6}$	-
Breakdown voltage		VBR 40.5 ± 5		V			
Crosstalk probability		-	1.5 5 1.5 5		%		
Recommended operating	voltage*5	Vop	V <sub>BR</sub> + 5			V	
Temperature coefficient at recommended		AT\/on	ΔTVop 47				mV/°C
operating voltage		дтуор					IIIV/ C
Recommended TE-cooler temperature   TTE_recom   -10			°C				

<sup>\*4:</sup>  $\lambda$ = $\lambda$ p, photon detection efficiency does not include crosstalk or afterpulses.

Note: The above characteristics were measured at the operating voltage that yields the listed gain. (See the data attached to each product.)


# - Connection example






<sup>\*5:</sup> Refer to the data provided with the product.

#### Photon detection efficiency vs. wavelength (typical example)




Photon detection efficiency does not include crosstalk or afterpulses.

#### **Gain, crosstalk probability, photon detection efficiency vs. overvoltage characteristics (typical example)**









KAPDB0561EA

MPPC characteristics vary with the operating voltage. Although increasing the operating voltage improves the photon detection efficiency and time resolution, it also increases the dark count and crosstalk at the same time, so an optimum operating voltage must be selected to match the application.


# Current vs. voltage characteristics of TE-cooler




# **Thermistor temperature characteristics**



# Cooling characteristics of TE-cooler



# Dimensional outlines (unit: mm)



# KAPDA0211EA

#### Precautions

· If necessary, incorporate appropriate protective circuits in power supplies, devices, and measuring instruments to prevent overvoltage and overcurrent.

KAPDA0210EA

#### Related products

#### MPPC modules C14455/C14456 series

The C14455/C14456 series are measurement modules capable of detecting low-level light using its built-in TE-cooled MPPC (S14422 series). These modules consist of a thermoelectrically cooled MPPC, an amplifier, a high-voltage power supply circuit, and a temperature control circuit. The photosensitive area is available in two sizes of \$1.5 mm and \$\phi 3.0 mm, and the signal output is analog for GA type and digital for GD type. The modules operate just by connecting them to an external power supply (±5 V). As the C14456 series is compact and lightweight, it is suitable for integration into devices (Heat dissipation measures are necessary).

Type no.	Aignal output	Built-in MPPC	Photosensitive area (mm)	Pixel pitch (µm)	
C14455-1550GA	Analog	S14422-1550DG	φ1.5		
C14455-1550GD	Digital	1514422-155000	Ψ1.5		
C14455-3050GA	Analog	S14422-3050DG	ф3.0	F0	
C14455-3050GD	Digital	1514422-303000	ψ3.0		
C14456-1550GA	Analog	S14422-1550DG	A1 F	50	
C14456-1550GD	Digital	514422-1550DG	φ1.5		
C14456-3050GA	Analog	S14422-3050DG	42.0	]	
C14456-3050GD	Digital	1514422-3030DG	ф3.0		



C14455 series



C14456 series

#### Related information

www.hamamatsu.com/sp/ssd/doc\_en.html

- Precautions
- Disclaimer
- · Metal, ceramic, plastic package products
- Technical note
- · MPPC
- · MPPC modules

MPPC is a registered trademark of Hamamatsu Photonics K.K. Information described in this material is current as of June 2022.

Product specifications are subject to change without prior notice due to improvements or other reasons. This document has been carefully prepared and the information contained is believed to be accurate. In rare cases, however, there may be inaccuracies such as text errors. Before using these products, always contact us for the delivery specification sheet to check the latest specifications.

The product warranty is valid for one year after delivery and is limited to product repair or replacement for defects discovered and reported to us within that one year period. However, even if within the warranty period we accept absolutely no liability for any loss caused by natural disasters or improper product use. Copying or reprinting the contents described in this material in whole or in part is prohibited without our prior permission.

# MAMATSU

www.hamamatsu.com

HAMAMATSU PHOTONICS K.K., Solid State Division

1126-1 Ichino-cho, Higashi-ku, Hamamatsu City, 435-8558 Japan, Telephone: (81)53-434-3311, Fax: (81)53-434-5184

ILIZO-I ICHINIO-CIRO, RIIGASIII-RU, RIAMMATSU CHORORATION: 300 Footbill Road, Bridgewater, NJ 08807, U.S.A.; Riephone: (1)908-231-0960, Fax: (1)908-231-1218 E-mail: usa@hamamatsu.com
Germany: HAMAMATSU CHORORATION: 300 Footbill Road, Bridgewater, NJ 08807, U.S.A., Telephone: (1)908-231-12128 E-mail: usa@hamamatsu.com
Germany: HAMAMATSU PHOTONICS DEUTSCHLAND GMBH.: Arzbergerstr. 10, 82211 Herrsching am Ammersee, Germany, Telephone: (49)8152-375-0, Fax: (49)8152-265-8 E-mail: info@hamamatsu.de
France: HAMAMATSU PHOTONICS FRANCE S.A.R.L.: 19, Rue du Saule Trapu, Parc du Moulin de Massy, 91882 Massy Cedex, France, Telephone: (33)1 69 53 71 10, Fax: (33)1 69 53 71 10 E-mail: info@hamamatsu.fr
United Kingdom: HAMAMATSU PHOTONICS UK LIMITED: 2 Howard Court, 10 Tewin Road, Welwyn Garden City, Hertfordshire AL7 18My, UK, Telephone: (44)1707-294888, Fax: (44)1707-325777 E-mail: info@hamamatsu.co.uk
North Europe: HAMAMATSU PHOTONICS STALIA S.R.L.: Strada della Moia, 1 int. 6, 20044 Arese (Milano), Italy, Telephone: (49)8-509 031 01, Fax: (39)02-93 58 17 33, Fax: (39)02-93 58 17 41 E-mail: info@hamamatsu.it
China: HAMAMATSU PHOTONICS (CHINA) CO., LTD.: 1201 Tower B, Jiaming Center, 27 Dongsanhuan Beilu, Chaoyang District, 100020 Beijing, RR. China, Telephone: (86)10-6586-6006, Fax: (86)10-6586-6006, F